

## **ACCU-CAL™ 50-LED Radiometer**

Consistent light curing requires periodic monitoring of light energy intensity and dosage levels. The ACCU-CAL™ 50-LED radiometer is simple to operate and offers accurate measurement of curing energy. The ACCU-CAL™ 50-LED can measure energy levels emitted from lightguides (3 mm, 5 mm, and 8 mm) and LED flood lamps. A spectral sensitivity range of 350 - 450 nm and intensity measurement from 1 mW/cm² to 40 W/cm², makes this unit ideal for measuring LED curing source energy levels. A specially designed photo-sensor assembly provides repeatable measurements and protection from high temperatures associated with some LED systems on the market.

## Simple to Operate ■ Set Screw Locks Lightguide in Place ■ PTB and NIST Traceable



ACCU-CAL™ 50-LED for measuring flood lamps only. PN 40519



ACCU-CAL<sup>™</sup> 50-LED for measuring LED spot lamps and flood lamps. PN **40505** 

## Three Reasons to Use a Radiometer

- Maintaining a Reliable Light-Curing Process A radiometer helps to ensure that a light-curing system is providing the intensity and dosage levels required for successful curing.
- Providing a Worker-Friendly Light-Curing Process The ACCU-CAL™ 50-LED is sufficiently sensitive to measure the intensity of stray or reflected energy (as little as 1 mW/cm²). Dymax recommends that worker UVA exposure not exceed 1 mW/cm². For reference, UV (320-395 nm) intensity on a sunny day can range from 2-6 mW/cm².
- Measuring Transmission Rates Through Substrates A radiometer can be used to measure the transmission
  rates of various wavelengths through substrates that sometimes absorb various frequencies of energy. To assure an
  effective curing process it is critical to measure the light intensity reaching the cure site below any intervening
  substrate.

SPECIFICATIONS	
Spectral Sensitivity	350 to 450 nm
Intensity Range	1 mW/cm <sup>2</sup> to 40 W/cm <sup>2</sup>
Resolution	Intensity (1 mW/cm²; to three significant digits) Dose (1 mJ/cm²)
Calibration Period	12 months
Operating Temperature Ranges	Optometer: +5 to +40°C Detector: 120°C continuous, Peak 200°C
Measurement Modes	Intensity (mW/cm²) Peak Intensity (mW/cm²) Dose (m J/cm²)
Light Sources	Lightguides (3 mm, 5 mm, and 8 mm), LED Flood Lamps
Power Supply	Two (2) AA batteries
Battery Life	250 hours (automatic shutoff after 1 hour)
Sensor Dimensions	Photo-Sensor Diameter = 9 mm Diameter = 37 mm Thickness = 8 mm Cable Length = 1 M
Meter Dimensions	145 mm (Length) x 63 mm (Width) x 30 mm (Thickness)

RADIOMETERS and ACCESSORIES		
Product	Part #	Description
ACCU-CAL™ 50-LED for LED Spot and Flood Units	40505	Complete radiometer with lightguide adapters (3 mm, 5 mm, and 8 mm) and lightguide simulator*; includes storage/carrying case
ACCU-CAL™ 50-LED for LED Flood Units	40519	Complete radiometer for LED flood and conveyor systems; includes storage/carrying case
Flood to Spot Adapter Kit	39554	Kit includes three lightguide adapters (3 mm, 5 mm, and 8 mm) and a lightguide simulator*
3 mm Lightguide Adapter	39556	Fits 3 mm ID lightguides (5 mm OD)
5 mm Lightguide Adapter	39557	Fits 5 mm ID lightguides (7 mm OD)
8 mm Lightguide Adapter	39558	Fits 8 mm ID lightguides (10 mm OD)
Lightguide Simulator	38408	Lightguide simulator (Fits all standard lightguide entrance fittings)

<sup>\*</sup>A lightguide simulator is used to measure direct spot lamp intensity (required to calculate lightguide transmission)

## **RADIOMETER CALIBRATION**

Dymax recommends calibrating the ACCU-CAL™ 50-LED radiometer annually to ensure proper operation of the instrument. Calibration services are available through Dymax. Please contact Dymax Customer Support for more information.



© 2009-2012 Dymax Corporation. All rights reserved. All trademarks in this guide, except where noted, are the property of, or used under license by Dymax Corporation, U.S.A.

Please note that most dispensing and curing system applications are unique. Dynax does not warrant the fitness of the product for the intended application. Any warranty applicable to the product, its application and use is strictly limited to that contained in Dynax's standard Conditions of Sale. Dynax recommends that any intended application be evaluated and tested by the user to insure that desired performance criteria are satisfied. Dynax is willing to assist users in their performance testing and evaluation by offering equipment trial rental and leasing programs to assist in such testing and evaluations. Data sheets are available for valve controllers or pressure pots upon request.