

**THINKY**

# Advancing the Reliability of the SMT Line Solder Paste Mixer

**Mix, Disperse, and Deaerate in Minutes.  
Optimized viscosity control using step mixing.**



**Support lead-free  
soldering**

**Planetary Centrifugal Mixer**

**THINKY MIXER**

**SR-500**

**Mix, Disperse, and Deaerate in Minutes.**

**5 level step mixing for optimized temperature and viscosity control.**

- Planetary Centrifugal Mixer provides solder vessel rotation on its axis and revolution around the mixer axis to produce powerful acceleration, ensuring simultaneous mixing, dispersing and deaerating. The resulting homogeneous dispersion of the solder powder produces not only a high quality solder but also removes even the smallest bubbles, which could cause solder paste splatter.
- Refrigerated solder reaches the ideal temperature quickly and can be used immediately. This eliminates condensation and reduces the time waiting for solder to its working temperature.
- Standard 500g solder containers can be loaded into the mixer directly.
- 5 level step mixing (speed and time) allows control over viscosity and temperature.
- It provides uniform paste consistency regardless of operator skill.
- Weight balance controls allow mixing of solder paste less than 500g in weight.



THINKY CORPORATION

**Headquarters** ----- 3-7-16 Iwamoto-cho Chiyoda-ku Tokyo # 101-0032, JAPAN Phone: +81-3-5821-7455 Fax: +81-3-3865-7833

**THINKY USA Inc.**----- 23151 Verdugo Drive Suite 107 Laguna Hills, CA 92653 Phone: (949) 768-9001 Fax: (949) 768-9003


**THINKY CHINA Inc.**--- Room 518 East building HaiAn Kafunuo mansion Shennan road Qianhai road Nanshan district Shenzhen Phone: (86) 755-86672181

# Solder Paste Mixer THINKY MIXER SR-500

SR-500  
Mixing

## Mix and Deaerate in Minutes. Control Viscosity and Temperature.

### Example of Step Mixing




150ml vessel with 500 g of solder



### Mixing Example




[Mixed by hand]



Bubbles are clearly visible and the solder powder is not homogeneously dispersed.



[Mixed by the SR-500]



Bubbles are terminated and the solder powder is homogeneously dispersed.

### SR-500 Basic Specifications

Model	SR-500	Maximum mixing capacity	150ml	Dimensions	H380×W300×D340*(mm) *Freight Locks included : D365mm
Product Name	Planetary Centrifugal Mixer THINKY MIXER	Maximum mixing mass	500g (NET)	Weight	Approx.18kg
System	Planetary propeller-less mixing system	Upper limit using a 300ml container	150ml, 500g (NET) 150ml, 560g (GROSS) *adaptor excluded		
Timer setting range	0 seconds, and 10sec to 30min	Safety Features	Door sensor, Vibration sensor, Revolution sensor		
Revolution speed	Max 1200rpm STD : Step1 Fixed 1000rpm, Step2 Fixed 500rpm STEP : 0rpm, 200-1200rpm	Power Supply	Single Phase AC230V±10 % 50Hz / 60Hz Power consumption Standby : approx.50VA Operating : max.900VA		
Rotation speed	Max 400rpm, Follows 1/3 of Revolution Speed	Operating Condition	Indoor use only, Elevation value within 2000m, Pollution degree 2		
Memory	5 memories (Each memory holds 5 sequential time and rpm steps.)	Operating Environment	10-35°C, 35-85%RH(Non-condensation)		

- Specification is subject to change without notification.
- Some types of mixing materials may be insufficiently mixed or defoamed (degassed).
- This unit is not designed to be explosion-proof. Do not mix materials that are dangerous or hazardous to humans.
- The mixing results may vary depending on process conditions or materials.



Included Adapters  
150ml vessel adapter (1 included)

- Visit our web site for product information and exhibition schedule  
<http://www.thinky.co.jp/en/>



THINKY Business Partner ;

## THINKY CORPORATION

Pioneer of planetary centrifugal mixers

Headquarters ----- 3-7-16 Iwamoto-cho Chiyoda-ku Tokyo # 101-0032, JAPAN  
Phone: +81-3-5821-7455 Fax: +81-3-3865-7833

THINKY USA Inc. ----- 23151 Verdugo Drive Suite 107 Laguna Hills, CA 92653  
Phone: (949) 768-9001 Fax: (949) 768-9003

THINKY CHINA Inc. --- Room 518 East building HaiAn Kafunuo mansion Shennan road  
Qianhai road Nanshan district Shenzhen  
Phone: (86) 755-86672181