



WHERE **PRECISION DRIVES PRODUCTION** 

# **PVA-1LTUV SPECIFICATIONS**

#### **Inside Dimensions:**

5.25" diameter x 11.75" high

## **Overall Outside Dimensions:**

8" diameter x 14" high

## **Body of Tank:**

Aluminum, black anodized

#### Gaskets:

(2) Teflon® encapsulated Viton® o-rings

# **Operating Air Pressure:**

0-70 PSI

#### Air Inlet:

Metal quick connect fitting

#### **Material Outlet:**

1/4" OD tube compression fitting

▲ 3/8" OD tube optional


# **PVA-1LTUV** 1 LITER BOTTLE PRESSURE RESERVOIR

Directions for use: Remove the two threaded thumbscrews and lift off the tank's lid. Place an uncapped material bottle in the center of the pressure tank. Return the lid to the top of the pressure tank while assuring that the dip tube is positioned inside the bottle of fluid. Tighten both thumbscrews evenly. Connect all material and air lines supplying pressure to the tank.

The PVA-1LTUV has many integrated features including:

- Safety air relief valve at 70 psi
- Disposable material path
- Accepts material packaged in bottles
- Safe for use with UV and anaerobic materials
- Top mounted air and material fittings

For more information on PVA's dispensing capabilities, please contact one of our sales representatives at (518) 371-2684.



One Mustang Drive Cohoes NY 12047 tel 518 371 2684 fx 518 371 2688 www.pva.net